

PRE-OWNED PHACO EMULSIFICATION SYSTEMS

Refurbished, like new, patient ready!

What Other Doctors Say

Thank you for helping us with the [Infiniti](#) for our center. You were patient and made sure we got what we wanted.☺☺☺

We installed it in our hospital and works excellent. I will want to buy more machines in the next few months.

Sincerely,☐ Solongoo TS, Conogol Trade, LLC Ulaanbaatar, Mongolia



With 65 INTRAFLOW Vision Control, it helps you gain insight into the phaco process. With 65 INTRAFLOW, it automatically optimize



With 65 INTRAFLOW Vision Control, it helps you gain insight into the phaco process. With 65 INTRAFLOW, it automatically optimize



With 65 INTRAFLOW Vision Control, it helps you gain insight into the phaco process. With 65 INTRAFLOW, it automatically optimize



With a 15.5" TFT 1040x512 Screen, 700mA High Power, Softing and up to 150W Trial
 With a 15.5" TFT 1040x512 Screen, 700mA High Power, Softing and up to 150W Trial



Since 2008, we have had a lot of phaco machines. Little sold with 2 top phaco, we have, foot
 Since 2008, we have had a lot of phaco machines. Little sold with 2 top phaco, we have, foot



SMO Sign. With 15.5" TFT 1040x512 Screen, 700mA High Power, Softing and up to 150W Trial
<http://www.cusseyequipment.com>